

**King Speedy
FLAT MOPPING SYSTEM**





King Speedy FLAT MOPPING SYSTEM



STEP BY STEP ASSEMBLY & OPERATING GUIDE



Select mop and cut-off colour-coded tabs to suit cleaning application




Quick and easy handle assembly into crown socket



Insert cir-clip into crown socket to lock-in handle. Screw tight to secure



Open clasp on mop holder and locate mop tab eyelets onto pins



Break mop frame to push mop onto frame and complete mop fixing with tabs either end



Lift up mop frame in break position





King Speedy FLAT MOPPING SYSTEM



STEP BY STEP ASSEMBLY & OPERATING GUIDE



Place mop and frame into clean solution



Place mop into wringer



Apply wringer arm to squeeze mop



Twist and drop mop to floor to lock frame ready for use



Keep mop and frame flat on floor



Mop can be used flat against skirting or stairs



Mop can also be used side-on against skirting or stairs



After use push foot onto pedal to break frame



With frame in break position, simply detach soiled mop into laundry basket



Bucket has built-in divider to separate clean and soiled solutions



King Speedy FLAT MOPPING SYSTEM



HANDLES / FRAMES & KING SPEEDY MOPS

KS40LM King Speedy flat mop - looped cotton White

KS40MF King Speedy microfibre flat mop plus grey scrub stripes White/Grey

KS40NF King Speedy microfibre flat mop - no fringe white

KS40EMF King Speedy economy microfibre flat mop Blue

KS40HFBLCH King Speedy flat mop system frame/handle Silver/Blue

KS40FB King Speedy frame Blue

KS40FG King Speedy frame Green

KS40FR King Speedy frame Red

KS40FY King Speedy frame Yellow



King Speedy FLAT MOPPING SYSTEM



101HO Aluminium 54" x 7/8" handle with colour coded grip Silver/Blue

101HOGN Aluminium 54" x 7/8" handle with colour coded grip Silver/Green

101HORD Aluminium 54" x 7/8" handle with colour coded grip Silver/Red

101HOYL Aluminium 54" x 7/8" handle with colour coded grip Silver/Yellow



MFTHBL Hy-Style telescopic handle (extends to 1.7m)
Silver/Blue

MFTHRD Hy-Style telescopic handle (extends to 1.7m)
Silver/Red

MFTHYL Hy-Style telescopic handle (extends to 1.7m)
Silver/Yellow

MFTHGN Hy-Style telescopic handle (extends to 1.7m)
Silver/Green / Blue

MFTHGY Hy-Style telescopic handle (extends to 1.7m)
Silver/Grey

